ProSeries® Door Hardware Service Procedure

6621, 6627, 6721, 6727, 6842, 6852, 7042, 7047, 7052 Series

The ProSeries® Door Hardware locks employ a construction technology similar to that used in the Rekeyables. It also allows for a uniform assembly and disassembly technique. Below is the step by step procedure for disassembling this version of padlock. The only exception to this procedure will be the IC version of the lock.

- Use the key to unlock the shackle, A. (If key is unavailable you will have to use another method to unlock the shackle).
- Use a 7/64" hexagonal wrench to remove the mounting screw located inside the toe side shackle hole.
- Holding the plug retainer, D, in place, lock the shackle, A, into the padlock body. (This relieves pressure on the actuator.)
- Remove the cylinder driver, K, with the cylinder, C.
- Remove the driver if it did not come out with the cylinder adapter and the cylinder.
- Remove the actuator, E.
- Remove the locking ball bearings, B, and shackle, A.

The order may be reversed to reassemble the lock. A light application of assembly grease may be used to hold the ball bearings in place during assembly.

If the lock only needs to be rekeyed, it is not necessary to remove the actuator, ball bearings, or shackle.

Two functions are available in the locks, NKR (Non Key Retaining) and NRK (Non Removable Key) and both functions are accomplished as a design feature of the actuator.

The NKR, non key retaining, function actuator used in the lock has a projection on one side. You should note the orientation of this projection when removing the actuator so that you can easily reinstall it during the reassembly process. Actuators are supplied with different sizes and two different styles have been used in the ProSeries® locks. Consult the Actuator section, page 26, of this manual for more detailed information.

The NRK non removable key, function actuator does not have a projection to help with orientation and you will have to rely on the position of the half-moon shaped actuator the tail of the cylinder contacts. Again, different sizes and styles are available for use in the ProSeries® locks, so consult the Actuator section, page 26, of this manual for more detailed information.

See component parts list on page 10.

Door Hardware Cylinder Drivers (K), page 26, 27.

 Lori
 298-0626

 Medeco
 298-0627

 Schlage
 298-0628

 Lockwood (Australia)
 298-0625

